

Checkmate Devices Ltd Corbin Way Gore Cross Business Park Bridport Dorset DT6 3UX

Telephone: 01308 423871



Roll Top Safes

Travel safes fitted with the ever-popular Roller Top are ideal for the transportation of cash and offer extreme ease of use. The operator need only place loose or bagged items into the roller top, turn the roller handle and the contents will drop into the safe compartment below.

Part No.	Description	L	W	Н	Kg
WCS1RT	Collect Standard Roll Top (120 x 80 opening) complete unit	270	155	420	9
WCS1A/RT	Collect Standard Roll Top (120 x 80 opening) safe & lid only	170	155	415	7
WCS1B/A	Additional Collect Base (Base plate & anchor fitting only)	210	155	80	2
WCS2RT	Commercial Roll Top (195 x 60 opening) 1 lock complete unit	325	180	320	9
WCS2RT2L	Commercial Roll Top (195 x 60 opening) 2 lock complete unit	325	180	320	9
WCS2RTLP	Commercial Short Roll Top (195 x 60 opening) 1 lock complete unit	325	180	270	8
WCS2F/A	Additional Commercial Base (Base plate & anchor fitting only)	325	180	30	2
WIS31/RT	Guardian Roll Top (235 x 80 opening) 2 lock complete unit	350	210	440	16
WIS31IB/A	Additional Guardian Base (Base plate & anchor fitting only)	350	210	30	3
WRTHD5	Heavy Duty Roll Top (255 x 125 opening) direct vehicle mounting	410	330	615	28

All dimensions are in mm (L & W dimensions = base plate 'footprint' - actual safe is approx 5% smaller)

L = length W = width H = height Kg = weight

Collect models require a key to enable the safe to be locked into the vehicle. **Commercial & Guardian** models autolock upon presentation to the base plate. The **Heavy Duty** model is designed for direct mounting to the vehicle floor.

Models that are offered with a 2nd lock option give enhanced security where the 1st lock is used to remove the safe & contents from the vehicle, then the 2nd removes the contents from the safe.

All locks are registered to Checkmate Devices Ltd and each is supplied with 2 keys. Keyed alike and master key systems are available upon request.

Base plates are anchored to the vehicle floor using a fixing kit (supplied).